# COMPACT





# M8/M12 ADAPTERS & T-COUPLERS

# Make the right connection!

The most innovative products emerge from the implementation of our customers' suggestions and needs. Like our range of M8/M12 adapters and T-couplers.

Whether it's the dark-bright switching of light barriers, the adaptation of M8 sensors to M12 connection cables, special pressure-switch circuits or bringing two separte signals to one port of a fieldbus box their uses are as numerous as the variations in the range.

#### **TECHNICAL DATA**

- Supply current: max. 4A
- Protection: IP67
- Temperature range: -25°C to 85°C

#### **BENEFITS**

- Allow for more flexibility
- Tailored to a wide range of customer applications
- Variety of circuit options:
  - M8 M8
  - M8 M12
  - M12 M12
  - M12 M8

#### **STANDARD ADAPTERS**

	Туре	Male	Female	Circuit diagram	Art. no.
	M12 Male – M12 Female	4 pole	4 pole	1	7000-41241-0000000
	M12 Male – M12 Female	5 pole	5 pole 3 0 0 0 0 0 1	2	7000-42281-0000000
	M12 Male – M8 Female	3 pole	3 pole	1 =	7000-42201-0000000
	M12 Male – M8 Female	4 pole	4 pole	1 ————————————————————————————————————	7000-42211-0000000
	M8 Male – M12 Female	3 pole	3 pole	1 ————————————————————————————————————	7000-88521-0000000
	M8 Male – M12 Female	4 pole	4 pole	1 ——— < 1 2 ——— < 2 3 ——— < 3 4 ——— < 4	7000-88531-0000000
	M8 Male – M8 Female	4 pole	3 pole	1 — — < 1 2 — — — 3 3 — — < 3 4 — — < 4	7000-88501-0000000
	M8 Male – M8 Female	3 pole 3 • 1	4 pole	1 ————————————————————————————————————	7000-88511-0000000

### **T-COUPLERS**



## **CONTACT US FOR MORE**

Murrelektronik has more custom models available. If you do not see what you are looking for, contact your Murrelektronik sales manager to discuss your application.